

TECAFIL PEEK VX natural - 1.75 mm - Filament

Chemical Designation

PEEK (Polyetheretherketone)

Colour

beige opaque

Density

1.3 g/cm³ (*2)

Main features

- inherent flame retardant
- very good chemical resistance
- good slide and wear properties
- good heat deflection temperature
- resistance against high energy radiation
- hydrolysis and superheated steam resistant

Target Industries

- electronics
- food technology
- automotive industry
- chemical technology
- mechanical engineering
- aircraft and aerospace technology

General material information	parameter	value	unit	norm	comment
Diameter		1,75 +/- 0,05	mm	-	(1) standard spool body
Spool measurements	holder	Ø 52	mm	-	(2) do not dry spool >120°C
Spool measurements	width	55	mm	-	(3) Ø 1,75mm
Spool measurements	outer diameter	Ø 200	mm	-	1)
Spool Material		Polycarbonate	-	-	2)
Filament Load per Spool		500	g	-	-
Filament Length per Spool		149	m	-	3)
Mechanical properties	parameter	value	unit	norm	comment
Tensile strength	5mm/min, Orientation XY	98,3	MPa	DIN EN ISO 527-2	1) (1) (*5), (*6)
Tensile strength	5mm/min, Orientation XZ	93,7	MPa	DIN EN ISO 527-2	2) (2) (*5), (*6)
Tensile strength	5mm/min, Orientation ZX	86,6	MPa	DIN EN ISO 527-2	3) (3) (*5), (*6)
Modulus of elasticity (tensile test)	5mm/min, Orientation XY	4006,7	MPa	DIN EN ISO 527-2	4) (4) (*5), (*6)
Modulus of elasticity (tensile test)	5mm/min, Orientation XZ	3869,7	MPa	DIN EN ISO 527-2	5) (5) (*5), (*6)
Modulus of elasticity (tensile test)	5mm/min, Orientation ZX	3657,2	MPa	DIN EN ISO 527-2	6) (6) (*5), (*6)
Elongation at yield (tensile test)	5mm/min, Orientation XY	5,4	%	DIN EN ISO 527-2	7) (7) (*5), (*6)
Elongation at yield (tensile test)	5mm/min, Orientation XZ	5,5	%	DIN EN ISO 527-2	8) (8) (*5), (*6)
Elongation at yield (tensile test)	5mm/min, Orientation ZX	4,8	%	DIN EN ISO 527-2	9) (9) (*5), (*6)
Elongation at break (tensile test)	5mm/min, Orientation XY	19,1	%	DIN EN ISO 527-2	10) (10) (*5), (*6)
Elongation at break (tensile test)	5mm/min, Orientation XZ	16,1	%	DIN EN ISO 527-2	11) (11) (*5), (*6)
Elongation at break (tensile test)	5mm/min, Orientation ZX	5,6	%	DIN EN ISO 527-2	12) (12) (*5), (*6)
Elongation at yield (flexural test)	2mm/min, Orientation XY	7,0	%	DIN EN ISO 178	13) (13) (*5), (*6)
Elongation at yield (flexural test)	2mm/min, Orientation ZX	6,7	%	DIN EN ISO 178	14) (14) (*5), (*6)
Flexural strength	2mm/min, Orientation XY	154,0	MPa	DIN EN ISO 178	15) (15) (*5), (*6)
Flexural strength	2mm/min, Orientation ZX	159,0	MPa	DIN EN ISO 178	16) (16) (*5), (*6)
Modulus of elasticity (flexural test)	2mm/min, Orientation XY	3550,0	MPa	DIN EN ISO 178	17) (17) (*5), (*6)
Modulus of elasticity (flexural test)	2mm/min, Orientation ZX	3740,0	MPa	DIN EN ISO 178	18) (18) (*5), (*6)
Elongation at break (flexural test)	2mm/min, Orientation XY	no break	%	DIN EN ISO 178	19) (19) (*5), (*6)
Elongation at break (flexural test)	2mm/min, Orientation ZX	no break	%	DIN EN ISO 178	20) (20) (*5), (*6)
Thermal properties	parameter	value	unit	norm	comment
Glass transition temperature		143	°C	ASTM D 3418	1) (1) (*2)
Melting temperature		343	°C	DIN EN ISO 11357	2) (2) (*2)
Deflection temperature	HDT-A	162	°C	ISO-R 75 Method A	3) (3) (*2)
Service temperature	short term	300	°C	-	4) (4) (*2)
Service temperature	long term	260	°C	-	5) (5) (*2)
Thermal expansion (CLTE)		5	10 ⁻⁵ K ⁻¹	DIN EN ISO 11359-1;2	6) (6) (*2)
Other properties	parameter	value	unit	norm	comment
Moisture absorption		0,03	%	DIN EN ISO 62	1) (1) (*2)
Flammability (UL94)	125x13x1,5mm	V0		DIN IEC 60695-11-10;	2) (2) (*2)
Melt flow index (MFI)	380°C / 5kg	10	g/10 min	DIN EN ISO 1133	3) (3) (*2)
Processing parameter	parameter	value	unit	norm	comment
Nozzle temperature		420 - 440	°C	-	(1) required
Max. melt temperature		470	°C	-	-
Print bed temperature		160 - 250	°C	-	-
Build chamber temperature		160 - 230	°C	-	1)
Nozzle diameter		0,4	mm	-	-
Print speed		20 - 30	mm/s	-	-
Fan speed		0	%	-	-
Predrying	parameter	value	unit	norm	comment
Drying temperature		120	°C	-	1) (1) (*4)

Drying time	8	h	-
-------------	---	---	---

- To achieve optimum mechanical properties, it is recommended to pre-dry the material with the above mentioned parameters.
- (*1) Values measured on injection moulded test specimens
 - (*2) Values measured on the raw material
 - (*3) The exact parameters depend on the printer used.
 - (*4) Do not exceed maximum drying temperature of 120°C
 - (*5) Properties tested on printed specimens
 - (*6) Specimens printed on Kumovis R1
- The filament should preferably be stored in dry, normal temperature rooms and protected from direct sunlight.

Our information and statements reflect to current state of our knowledge and shall inform about the products and their applications. They do not assure or guarantee chemical resistance, quality of products and their merchantability in a legally binding way. Our products are not defined for use in medical or dental implants. Existing commercial patents have to be observed. The customer is solely responsible for the quality and suitability of products for the application and has to test usage and processing prior to use. Data sheet values are subject to periodic review, the most recent update can be found at ensingerplastics.com. Technical changes reserved. European-made or imported varieties comply with REACH Regulation 1907/2006 / EC as amended Unless otherwise noted, these values were determined by tests on injection moulded samples, dry as moulded. The corresponding values and information are no minimum or maximum values, but guideline values that can be used primarily for comparison purposes for material selection. These values are within the normal tolerance range of product properties and do not represent guaranteed property values. Therefore they shall not be used for specification purposes. In order to achieve optimum mechanical properties, pre-drying of the material is recommended with the parameters mentioned above Filaments should preferably be stored in dry rooms at normal temperatures and be protected from direct sunlight.