

Polypropylene RP 340S

Sub-group:

Random Copolymer

Description:

RP 340S is a very high fluidity Random Copolymer, suitable for fast cycle thin wall injection molding. It exhibits excellent processability and transparency, good balance of rigidity/impact and very low odor and flavor transfer.

Applications:

Injection of high transparency and thin-walled parts.

Processing:

Injection Moulding

Control Property:

	ISO Method	Units	Values
Melt Flow Rate (230°C/2.16 kg)	1133	g/10 min	45

Typical Properties^a:

	ISO Method	Units	Values
Density	1183-1	g/cm ³	0.902
Flexural Modulus – 1% secant	178	MPa	1250
Tensile Strength at Yield	527-1	MPa	31
Tensile Elongation at Yield	527-1	%	12
Rockwell Hardness (R Scale)	2039-2	-	85
Notched Izod Impact Strength at 23°C	180	kJ/m ²	3.0
Deflection Temperature under Load at 0.455 MPa	75-1/75-2	°C	78

a) Injection molded specimen according to ISO 294.

b) Specimen thickness: 1 mm.

Final Remarks:

1. This resin meets the requirements for olefin polymers as defined in 21 CFR, section 177.1520 issued by FDA – Food and Drug Administration in force on the date of publication of this specification. The additives present are covered in appropriate regulation by FDA.
2. The information presented in this Data Sheet reflects typical values obtained in our laboratories, but should not be considered as absolute or as warranted values. Only the properties and values mentioned on the Certificate of Quality are considered as guarantee of the product.
3. In some applications, Braskem has developed tailor-made resins to reach specific requirements.
4. In case of doubt regarding utilization, or for other applications, please contact our Technical Assistance.
5. For information about safety, handling, individual protection, first aids and waste disposal, please see MSDS. CAS Registry number: 9010-79-1
6. The mentioned values in this report can be changed at any moment without Braskem previous communication.
7. Braskem does not recommend this grade for packages, parts or any kind of product manufacture that will be used for storage or contact with solution that will have internal contact with human body.
8. This resin does not contain the substance Bisphenol A (BPA, CAS # No. 80-05-7) in its composition.