

LEXANTM HEALTHCARE RESIN HPS2REU

REGION EUROPE

DESCRIPTION

LEXAN HPS2REU is a high flow polycarbonate (PC) with an MVR (300°C/1.2kg) of 17. This is a biocompatible (ISO 10993 or USP Class VI) grade for medical devices and pharmaceutical applications. It is gamma and e-beam sterilizable, contains mold release and adheres to our healthcare management of change policy. Available in Europe only.

TYPICAL PROPERTY VALUES

PROPERTIES	TYPICAL VALUES	UNITS	TEST METHODS
MECHANICAL			
Tensile Stress, yield, 50 mm/min	63	MPa	ISO 527
Tensile Stress, break, 50 mm/min	70	MPa	ISO 527
Tensile Strain, yield, 50 mm/min	6	%	ISO 527
Tensile Strain, break, 50 mm/min	110	%	ISO 527
Tensile Modulus, 1 mm/min	2350	MPa	ISO 527
Flexural Stress, yield, 2 mm/min	90	MPa	ISO 178
Flexural Modulus, 2 mm/min	2300	MPa	ISO 178
IMPACT			
Izod Impact, unnotched 80*10*3 +23°C	NB	kJ/m ²	ISO 180/1U
Izod Impact, unnotched 80*10*3 -30°C	NB	kJ/m ²	ISO 180/1U
Izod Impact, notched 80*10*3 +23°C	70	kJ/m ²	ISO 180/1A
Izod Impact, notched 80*10*3 -30°C	12	kJ/m ²	ISO 180/1A
Charpy 23°C, V-notch Edgew 80*10*3 sp=62mm	70	kJ/m ²	ISO 179/1eA
Charpy -30°C, V-notch Edgew 80*10*3 sp=62mm	10	kJ/m ²	ISO 179/1eA
Charpy 23°C, Unnotch Edgew 80*10*3 sp=62mm	NB	kJ/m ²	ISO 179/1eU
Charpy -30°C, Unnotch Edgew 80*10*3 sp=62mm	NB	kJ/m ²	ISO 179/1eU
Charpy Impact, notched, 23°C	35	kJ/m ²	ISO 179/2C
THERMAL			
Vicat Softening Temp, Rate A/50	150	°C	ISO 306
Vicat Softening Temp, Rate B/50	140	°C	ISO 306
Vicat Softening Temp, Rate B/120	140	°C	ISO 306
HDT/Be, 0.45MPa Edgew 120*10*4 sp=100mm	130	°C	ISO 75/Be
HDT/Ae, 1.8 MPa Edgew 120*10*4 sp=100mm	120	°C	ISO 75/Ae
Relative Temp Index, Elec	130	°C	UL 746B
PHYSICAL			
Mold Shrinkage on Tensile Bar, flow	0.5 – 0.7	%	SABIC method
Density	1.2	g/cm ³	ISO 1183
Water Absorption, (23°C/sat)	0.35	%	ISO 62
Moisture Absorption (23°C / 50% RH)	0.15	%	ISO 62
Melt Volume Rate, MVR at 300°C/1.2 kg	17	cm ³ /10 min	ISO 1133
OPTICAL			
Light Transmission, 2.54 mm	88 – 90	%	ASTM D 1003
Haze, 2.54 mm	<0.8	%	ASTM D 1003



PROPERTIES	TYPICAL VALUES	UNITS	TEST METHODS
Refractive Index	1.586	-	ISO 489
INJECTION MOLDING			
Drying Temperature	120	°C	
Drying Time	2 – 4	hrs	
Maximum Moisture Content	0.02	%	
Melt Temperature	280 – 310	°C	
Nozzle Temperature	270 – 290	°C	
Front - Zone 3 Temperature	280 – 310	°C	
Middle - Zone 2 Temperature	270 – 290	°C	
Rear - Zone 1 Temperature	260 – 280	°C	
Hopper Temperature	60 – 80	°C	
Mold Temperature	80 – 110	°C	