

Hostaform LGC 90-QX - POM

Description

Material code according to ISO 1043-1: POM Acetal copolymer reinforced with 25 weight percent long glass fibers. The fibers are chemically coupled to the POM matrix. The pellets are cylindrical and normally as well as the embedded fibers 10 mm long. Parts molded of CELSTRAN have outstanding mechanical properties such as high strength and stiffness combined with high heat deflection. The notched impact strength is increased at elevated and low temperatures due to the fiber skeleton built in the parts. The long fiber reinforcement reduces creep significantly. The very isotropic shrinkage in the molded parts minimizes the warpage. Complex parts can be manufactured with high reproducibility by injection molding. Application field: Functional/structural parts for automotive

Physical properties	Value	Unit	Test Standard
Density	1590	kg/m ³	ISO 1183
Mechanical properties	Value	Unit	Test Standard
Tensile modulus	10000	MPa	ISO 527-2/1A
Tensile stress at break, 50mm/min	170	MPa	ISO 527-2/1A
Tensile strain at break, 5mm/min	2.36	%	ISO 527-2/1A
Flexural modulus, 23°C	9200	MPa	ISO 178
Flexural strength, 23°C	265	MPa	ISO 178
Charpy notched impact strength, 23°C	35	kJ/m ²	ISO 179/1eA

Typical injection moulding processing conditions

Pre Drying	Value	Unit	Test Standard
Necessary low maximum residual moisture content	0.15	%	-
Drying time	3	h	-
Drying temperature	80 - 90	°C	-
Temperature	Value	Unit	Test Standard
Feeding zone temperature	20 - 50	°C	-
Zone1 temperature	180 - 195	°C	-
Zone2 temperature	190 - 200	°C	-
Zone3 temperature	195 - 205	°C	-
Zone4 temperature	195 - 205	°C	-
Nozzle temperature	195 - 205	°C	-
Melt temperature	195 - 205	°C	-
Mold temperature	70 - 110	°C	-
Hot runner temperature	195 - 205	°C	-
Pressure	Value	Unit	Test Standard
Back pressure max.	30	bar	-
Speed	Value	Unit	Test Standard
Injection speed	medium	-	-
Screw Speed	Value	Unit	Test Standard
Screw speed diameter, 40mm	50	RPM	-
Screw speed diameter, 55mm	35	RPM	-
Screw speed diameter, 75mm	25	RPM	-

Other text information

Pre-drying

It is normally not necessary to dry CELSTRAN POM. However, should there be surface moisture (condensate) on the molding compound as a result of incorrect storage, drying is required. A circulating air drying cabinet can be used for this purpose if the gra

Longer pre-drying times/storage

The product can then be stored in standard conditions until processed.

Hostaform LGC 90-QX - POM

Characteristics

Special Characteristics

High flow

Delivery Form

Pellets

Product Categories

Glass reinforced

Regional Availability

North America, Europe, Asia Pacific

Processing

Injection molding

Contact Information

General Disclaimer

NOTICE TO USERS: Values shown are based on testing of laboratory test specimens and represent data that fall within the standard range of properties for natural material. These values alone do not represent a sufficient basis for any part design and are not intended for use in establishing maximum, minimum, or ranges of values for specification purposes. Colorants or other additives may cause significant variations in data values. Properties of molded parts can be influenced by a wide variety of factors including, but not limited to, material selection, additives, part design, processing conditions and environmental exposure. Any determination of the suitability of a particular material and part design for any use contemplated by the users and the manner of such use is the sole responsibility of the users, who must assure themselves that the material as subsequently processed meets the needs of their particular product or use. To the best of our knowledge, the information contained in this publication is accurate; however, we do not assume any liability whatsoever for the accuracy and completeness of such information. The information contained in this publication should not be construed as a promise or guarantee of specific properties of our products. It is the sole responsibility of the users to investigate whether any existing patents are infringed by the use of the materials mentioned in this publication. Moreover, there is a need to reduce human exposure to many materials to the lowest practical limits in view of possible adverse effects. To the extent that any hazards may have been mentioned in this publication, we neither suggest nor guarantee that such hazards are the only ones that exist. We recommend that persons intending to rely on any recommendation or to use any equipment, processing technique or material mentioned in this publication should satisfy themselves that they can meet all applicable safety and health standards. We strongly recommend that users seek and adhere to the manufacturer's current instructions for handling each material they use, and entrust the handling of such material to adequately trained personnel only. Please call the telephone numbers listed for additional technical information. Call Customer Services for the appropriate Materials Safety Data Sheets (MSDS) before attempting to process our products. The products mentioned herein are not intended for use in medical or dental implants.

Trademark

© 2014 Celanese or its affiliates. All rights reserved. (Published 27.July.2016). Celanese®, registered C-ball design and all other trademarks identified herein with ®, TM, SM, unless otherwise noted, are trademarks of Celanese or its affiliates. Fortron is a registered trademark of Fortron Industries LLC.
